

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19164-0027](#)  
**Status:** **Active**  
**Overview:** Perma-Seal™ Terminals  
**Description:** Perma-Seal™ Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 5/16" (M8)

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19164](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Perma-Seal™ Terminals](#)  
 Product Name Perma-Seal™  
 Type Ring  
 UPC 800753113152

**Physical**


Barrel Type Closed  
 Insulation NiAc™  
 Material - Plating Mating Tin  
 Net Weight 1.234/g  
 Packaging Type Bag  
 Stud Size 5/16" (M8)  
 Wire Insulation Diameter 5.97mm  
 Wire Size AWG 14, 16  
 Wire Size mm² 1.23 - 1.94

**Material Info**

Old Part Number SB-225-56

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
 Sales Drawing SD-19164-026



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[19164Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Power Crimp Tool Head for Terminals 10-22 AWG Wire	<a href="#">0640057400</a>
PremiumGrade™ Hand Crimp Tool	<a href="#">0640017400</a>