



Label mount with label (figures)

Part no. M22-XCK2

Article no. 279435



Powering Business Worldwide™

Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Single unit/Complete unit			Single unit
Name			0-1-0-2-0-3-0-4
For use with			4-way selector switch actuators
Connection to SmartWire-DT			no

General

Standards			IEC/EN 60947 VDE 0660
Climatic proofing			Damp heat, constant to IEC 60068-2-78 Damp heat, cyclic to IEC 60068-2-30
Ambient temperature		°C	
Open		°C	- 25 - + 70
Mounting position			As required

Technical data ETIM 4.0

Height			60
External diameter		mm	0
Width		mm	60
ISO symbol inscription			-
Form			quadratic
Inscription			-
Color			Silver

Additional product information (links)

IL04716002Z (AWA1160-1745) RMQ-Titan System		
IL04716002Z (AWA1160-1745) RMQ-Titan System	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2011_03.pdf	
Labeleditor	ftp://ftp.moeller.net/MFD/EASY-SOFT-PRO/labeleditor_206.exe	