



Datasheet

LED Indicator Lamp

ENGLISH

RS ITEM NO 209-636



LED/Multiled	LED	Optimum voltage (V)	28Vac/dc	Intensity	65mcd
Mounting Size	10x21	Rectifier	-		
Mounting Finish	BA9s	AC current	-		
Protection	-	DC current	17mA		
Mount Holder	-	Voltage Tolerance(%)	10%		
Chip Qty	-	Optimum temperature (°C)	-25°C...+60°C		
Indicator colour	Red	Storage temperature (°C)	-25°C...+60°C		
Wavelength (nm)	635	Contact Tab	Ba9s Base Cap		



Dimension in mm (typical), not to scale.
We reserve the right to make changes without further notice to this product to improve reliability, function or design