

Datasheet

Type G - British Grey 6 Gang Trailing Socket 2m Cable, 13A, 230 V ac Fused

RS Stock 249-4592



Specification:

Voltage Rating (Nominal)	230V rms
Maximum Current Rating	13A (7A Fuse fitted)
Power Consumption	Negligible
Lead Length	2m
Surge Handling (8/20us) [Per Element]	13.5kA [4.5kA]
Average Attenuation, Symmetric 1-30MHz (dB)	-20
Voltage Protection Level (U _p) 8/20us	900V@3kA 8/20us
Response Time	<10ns
BS6651:1999 Annex C Location Category	A & B