

3VU13 CIRCUIT BREAKER SETTING RANGE: 0.1-0.16A
AUX.SWITCH: 1NO+1NC FOR TRANSFORMER LINE SIDE
PROT.

Certificates/ approvals:

General Product Approval



GOST



KETI

Test Certificates

[Special Test Certificate](#)

Shipping Approval



LRS

other

[Confirmation](#)

[Declaration of Conformity](#)

[other](#)

[Environmental Confirmations](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WWW/view/en/3VU1340-1TB00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VU1340-1TB00

last change: