





SPECIFICATIONS	
CONTACT RATING	MIN. 100mA @ 5VAC/DC
	MAX. 3A @ 125VAC
INITIAL CONTACT RESISTANCE	20MILLIOHMS MAX AT 1A, 2-4 VDC
INSULATION RESISTANCE	100 MEGAOHMS MIN AT 500VDC
DIELECTRIC STRENGTH	1000 VAC, 1 MINUTE
ELECTRICAL LIFE	5000 OPERATIONS
OPERATING TEMPERATURE	-20°C TO 80°C
STORAGE TEMPERATURE	-20°C TO 80°C
RECOMMENDED SOLDER TEMP.	HAND SOLDER 420°C MAX, 3 SECONDS MAX.



SECTION A-A



RECOMMENDED PANEL CUTOUT

SPST	NO	RED	MSP103C204	1825516-4
SPST	NO	BLACK	MSP103C004	1825516-3
SPST	NO	RED	MSP103C04	1825516-2
SPST	NC	BLACK	MSP103B04	1825516-1
TYPE	MOMENTARY ACTION	ACTATOR BUTTON COLOR	ALCO P/N	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ZITTO 01DEC05		 TE Connectivity	
		CHK M.ZITTO 01DEC05			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD M.ZITTO 01DEC05		SWITCH, PUSHBUTTON MSP103, SILVER —	
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		—			
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A2	CAGE CODE —
		WEIGHT —		DRAWING NO C-1825516	
CUSTOMER DRAWING				SCALE 3:1	SHEET 1 of 1
				REV A1	