

Plug - PTPM 0,2/ 5-P-2,5 PA CAT5 - 1811161

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plug component, Nominal current: 2 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.5 mm, Color: black, Contact surface: Tin




Why buy this product

- Can be plugged into THR and SMD base strips
- Spring-cage and pierce contact technology
- Miniature plug with 2.5 mm pitch



Key commercial data

Packing unit	100 pc
GTIN	 4 046356 709101
Weight per Piece (excluding packing)	2.22 g
Custom tariff number	85366990
Country of origin	United States

Technical data

Dimensions

Pitch	2.5 mm
-------	--------

General

Range of articles	PTPM 0,4/...-P
Insulating material group	III
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	40 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	2 A

Plug - PTPM 0,2/ 5-P-2,5 PA CAT5 - 1811161

Technical data

General

Nominal cross section	0.14 mm ²
Maximum load current	2 A
Insulating material	PA/PC
Inflammability class according to UL 94	V0/V2
Number of positions	4

Connection data

Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	0.14 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max.	26
Maximum AWG according to UL/CUL	26
Wire diameter incl. insulation	1 mm (Terminal block is tested with PVC insulation - other insulation materials available on request)

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Plug - PTPM 0,2/ 5-P-2,5 PA CAT5 - 1811161

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized		
	B	D
mm ² /AWG/kcmil	26	26
Nominal current I _N	2 A	2 A
Nominal voltage U _N	50 V	50 V


cUL Recognized		
	B	D
mm ² /AWG/kcmil	26	26
Nominal current I _N	2 A	2 A
Nominal voltage U _N	50 V	50 V

cULus Recognized		
------------------	--	--


Drawings

Plug - PTPM 0,2/ 5-P-2,5 PA CAT5 - 1811161

Dimensioned drawing



Diagram



Derating curve for: PTPM 0,2/...-P-2,5 with PTSM 0,5/...-HH-2,5-THR R..