

2198UOI025P60-40x17

EAN 4031582300284

Fixed castor, Fork made of pressed steel, bright zinc plated, blue passivated, axle riveted, plate fitting.
Wheel centre made of Polyamide, plain bearing

Technical Data

Wheel diameter	25 mm
Width of Tread	13 mm
Size of Plate	40 x 17 mm
Plate hole centres	30 mm
Plate hole	4,5 mm
Overall height	28 mm
Temperature	- 40 / + 80 °C
Standard	EN 12528
Weight	0.018 kg
Hardness of tread	D 75 Shore
Load capacity	25 kg
Load capacity (static)	50 kg

Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

