

Datasheet

RS Pro Nitrile Rubber Flexible Tube, Black, 10mm External Diameter, 50m Long, Compressed Air Applications

RS Stock No: **340-0560**



Product Details

RS Pro nitrile rubber flexible tube is 50 m long and has an external diameter of 10 mm. This tube in black colour, is suitable for compressed air applications.

Features and Benefits

- Excellent resistance to aliphatic based hydrocarbon fluids
- Low gas permeation
- Good resistance to aromatic solvents and alcohols
- High tear and abrasion resistance
- Intended for non-pressure applications

**Specifications:**

Bend Radius	34 mm
Colour	Black
Inner Diameter	7 mm
Length	50 m
Material	Nitrile Rubber
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Operating Temperature Range	-20 to +100°C
Outer Diameter	10 mm
Reinforced	No
Suitable Applications	Compressed Air