

Interface module - UMK- EC56/56-XUL - 2975641

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, for ELCO connector, for mounting on NS 35/7.5 or NS 32, with pin strip 8016 left, no. of positions 56



Key commercial data

Packing unit	1 pc
GTIN	4 017918 089054
Weight per Piece (excluding packing)	293.5 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Width	157.5 mm
Height	77 mm
Depth	58.5 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	50 V AC/DC
Max. current carrying capacity per branch	2 A
Number of positions	56
Test voltage contact/contact	0.8 kV
Mounting position	any
Standards/regulations	DIN VDE 0110
Pollution degree	2

Interface module - UMK- EC56/56-XUL - 2975641

Technical data

General

Surge voltage category	II
------------------------	----

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Interface module - UMK- EC56/56-XUL - 2975641

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 

Drawings

Interface module - UMK- EC56/56-XUL - 2975641

