

Slide Switches

ASE, ASF Series

- Bifurcated double wipe contacts, also for telecom grade switching
- ASF for auto insertion on standard IC equipment



Number of poles	2, 4, 6
Number of throws	2, 3 (available in 4 pole only)
Contact timing	Make before Break
Right angle versions	Yes
Mounting style	SMT, THT
Actuator style	ASF: Flush top actuator ASE: Extended top or side ASFO: Flush top or side
Flush actuator version	ASF: Yes, ASE: No
Tape seal	ASF: Yes, ASE: No
Contact rating	Gold: 20 mA @ 20 Vdc Silver: 300 mA @ 115 Vac, 28 Vdc
Electrical endurance	10,000 ops.
Operating temperature range	-40...+80°C
Dimensions (LxWxH)	refer to catalogue
Packaging	Tube

S, SE Series

- Compact slide switch
- S: unsealed
SE: sealed (IP 67)



Number of poles	1 or 2
Number of throws	1,2
Contact timing	Break before Make
Right angle versions	Yes
Mounting style	SMT, THT
Actuator style	SE: Actuator with boot sealing
Flush actuator version	No
Tape seal	No
Contact rating	20 mA @ 20 Vdc
Electrical endurance	10,000 ops.
Operating temperature range	-20...+80°C
Dimensions (LxWxH)	9.5 x 5 x 8.0 mm
Packaging	Tray, Tape and Reel

STS, SDS Series

- Miniature slide switch
- STS: economy grade
SD: instrumentation grade
- Low profile



Number of poles	1 or 2
Number of throws	up to 6
Contact timing	Make before Break
Right angle versions	Yes
Mounting style	THT
Actuator style	SDS: on request
Flush actuator version	No
Tape seal	No
Contact rating	300 mA @ 125 Vac
Electrical endurance	10,000 ops.
Operating temperature range	-15...+60°C
Dimensions (LxWxH)	refer to catalogue
Packaging	Bulk

Slide switch

Number of poles	
Number of throws	
Contact timing	
Right angle versions	
Mounting style	
Actuator style	
Flush actuator version	
Tape seal	
Contact rating	
Electrical endurance	
Operating temperature range	
Dimensions (LxWxH)	
Packaging	

TSS Series

- Single or dual actuator



Number of poles	up to 4
Number of throws	1 or 2
Contact timing	Break before Make
Right angle versions	Yes
Mounting style	THT
Actuator style	Standard
Flush actuator version	Yes
Tape seal	No
Contact rating	20 mA @ 20 Vdc
Electrical endurance	80,000 ops.
Operating temperature range	-20...+80°C
Dimensions (LxWxH)	refer to catalogue
Packaging	Bulk

MSS, MSSA Series

- Instrumentation grade



Number of poles	up to 6
Number of throws	up to 4
Contact timing	Make before Break
Right angle versions	Yes
Mounting style	THT
Actuator style	Standard / MSSA: Position snap
Flush actuator version	No
Tape seal	No
Contact rating	Gold: 20 mA @ 20 Vdc Silver: 300 mA @ 125 Vac
Electrical endurance	15,000 ops.
Operating temperature range	-20...+85°C
Dimensions (LxWxH)	refer to catalogue
Packaging	Tray

MSSA-01/04 Series

- Instrumentation grade
- Top and side actuator



Number of poles	up to 2
Number of throws	2
Contact timing	Break before Make
Right angle versions	Yes
Mounting style	THT
Actuator style	Standard
Flush actuator version	Yes
Tape seal	No
Contact rating	Gold: 20 mA @ 20 Vdc Silver: 3A@115Vac, 1.5A@230Vac
Electrical endurance	30,000 ops.
Operating temperature range	-20...+85°C
Dimensions (LxWxH)	MSSA1: 11.9 x 6.4 x 8 mm MSSA2: 11.9 x 11.4 x 8 mm
Packaging	Bulk