

General Information

Extended Product Type:	216-C4
Product ID:	2CMA193520R1000
EAN:	7392696935203
Catalog Description:	Connector, 4h,16A, IP44, 2P+E
Long Description:	Connector, earthing sleeve position 4h, rated current 16A, IP44 splashproof, 2-poles+earth, 50 - 60 Hertz, color code yellow

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Connectors

Ordering

EAN:	7392696935203
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	75 mm
Product Net Height:	75 mm
Product Net Length:	134 mm
Product Net Depth:	75 mm
Product Net Weight:	0.157 kg

Container Information

Package Level 1 Width:	138 mm
Package Level 1 Length:	285 mm
Package Level 1 Height:	120 mm
Package Level 1 Gross Weight:	0.157 kg
Package Level 1 EAN:	7392696935203
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, compression gland
Cable Cross-Section:	1.0 ... 2.5 mm ²
Color:	Yellow
Degree of Protection:	IP44
Enclosure Material:	Polyamide
Frequency (f):	60 Hz
Function:	Connector
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216-C4
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	C
Product Name:	Industrial Connector
Protection Type:	Splashproof
Rated Current (I _n):	16 A
Rated Voltage (U _r):	100 ... 130 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Connectors
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2416179

UNSPSC: 39120000

