

Datasheet

RS Pro Type F - German Schuko 6 Gang Trailing Socket, 2m Cable Filtered, 12.5A, 250 V ac Fused

RS Stock No: **374-200**



Product Details

RS Pro type F - German Schuko trailing socket is an ideal solution for home, office and industrial use. This surge and RFI protected socket features a 2 m lead fitted with a CEE7/7 Schuko type F plug feeding 6 CEE7/4 Schuko type F sockets in an aluminium case for high impact resistance and long life. The internal surge suppressors have been tested against worst case conditions as defined in International standards.

Features and Benefits

- Red status indication to show mains power/fuse OK
- Voltage rating (Nominal) of 230 V rms
- Maximum current rating of 12.5 A
- Power consumption: negligible
- Lead length of 2 m
- Surge handling (8/20 μ s) (per socket): 19.5 kA
- Average attenuation, symmetrical 1 to 30 MHz (dB): -50
- Voltage protection level (Up) 8/20 μ s of 900 V at 3 kA 8/20 μ s
- Response time of <10 ns
- Annex C Location category A and B approved

**Specifications:**

Cord Length	2 m
Corded	Yes
Current Rating	12.5 A
Filtered	Yes
Fused	Yes
Mains Plug Type	CEE7/7/Schuko
Number of Sockets	6
Power Indicator	Yes
Socket Type	Type F - German Schuko
Surge Protection	Yes
Switchable	Yes
Voltage Rating	250 V ac
Wired	Yes
Standards Met	RoHS Compliant