

ITT 3000 W 400 V-01X0 S

HALOTHERM | Infrared halogen lamps, quartz clear



Areas of application

- Plastics, paper and printing industries
- Drying paint and varnishes
- Coil coating
- Keeping food warm in restaurants

Product benefits

- Short response time
- High efficiency
- Precise controllability
- Long lamp life



Product datasheet

Technical data


Electrical data

Nominal wattage	3000.00 W
Nominal voltage	400 V
Nominal current	7.5 A
Lamp current	7.50000 A
Construction voltage	400 V

Photometrical data

Color temperature	2350 K
-------------------	--------

Dimensions & weight



Diameter	10.0 mm
Length	798.0 mm
Filament length	705.00 mm

Lifespan

Lifespan	5000 h
----------	--------

Additional product data

Base (standard designation)	X
-----------------------------	---

Capabilities

Burning position	Any
------------------	-----

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321645876	ITT 3000 W 400 V- 01X0 S	Role 1	45 mm x 45 mm x 1115 mm	2.26 dm ³	354.00 g
4008321645883	ITT 3000 W 400 V- 01X0 S	Shipping carton box 12	150 mm x 190 mm x 1120 mm	31.92 dm ³	2684.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.