

## Datasheet

# RS Pro Digital & Programmable HVAC Thermostat, 1 (Weekends) days, 5 (Weekdays) days

RS Stock No: 719-4159



## Product Details

RS Pro digital and programmable HVAC thermostat comes with LCD display for effective measurements. The large backlit LCD screen displays the set temperature, room temperature and time of day simultaneously. It is suitable for operating temperatures ranging from +5 to +35°C. This device can be programmed for 1 (Weekends) day and 5 (Weekdays) days. It features vacation mode and hold duration mode for added comfort and energy saving.

## Features and Benefits

- Large backlit LCD display screen
- The screen displays the set temperature, room temperature and time of day simultaneously
- Permanent user setting and program setting retention during power loss
- Optional Celsius or Fahrenheit display
- Both vacation mode and hold duration mode available for comfort and energy saving
- Separate 5 day (weekday) and 1 day/1 day) (Saturday and Sunday) programming with four separate time/temperature periods per day
- Display temperature recalibrates
- Powered by 2 x AA batteries (not supplied)



ENGLISH

### Specifications:

Additional Features	Hold Duration Mode, Holiday Mode, LCD Display
Contact Rating	5 A
Contact Voltage	230 V ac
Maximum Temperature	+35°C
Minimum Temperature	+5°C
Program Duration	1 Day (Weekends), 5 Days (Weekdays)
Supply Voltage	3 V dc (2 x AA Batteries)
Temperature Range	+5 to +35°C