


Soldering Irons and Tips

Magnastat Controlled Low Voltage Soldering Irons



Soldering Tips for TCPS, TCP 12, TCP 24 and FE 50M (continued)

Order No.	Model	Description	Width A
4PTF7	PT F7	Round tip sloped 370°C	Ø 1,2 mm
4PTF8	PT F8	Round tip sloped 425°C	Ø 1,2 mm
4PTAA7	PT AA7	Round tip sloped 370°C	Ø 1,6 mm
4PTAA8	PT AA8	Round tip sloped 425°C	Ø 1,6 mm
4PTAA9	PT AA9	Round tip sloped 480°C	Ø 1,6 mm
4PTBB7	PT BB7	Round tip sloped 370°C	Ø 2,4 mm
4PTBB8	PT BB8	Round tip sloped 425°C	Ø 2,4 mm
4PTBB9	PT BB9	Round tip sloped 480°C	Ø 2,4 mm
4PTCC7	PT CC7	Round tip sloped 370°C	Ø 3,2 mm
4PTCC8	PT CC8	Round tip sloped 425°C	Ø 3,2 mm
4PTCC9	PT CC9	Round tip sloped 480°C	Ø 3,2 mm
4PTDD7	PT DD7	Round tip sloped 370°C	Ø 5,0 mm
4PTDD8	PT DD8	Round tip sloped 425°C	Ø 5,0 mm
4PTDD9	PT DD9	Round tip sloped 480°C	Ø 5,0 mm

If other temperature or tips are required use PT / LT adapter see page 101.

Weller WDC – Dry Cleaner



Order No.	Model	Description
005 15 124 99	WDC	Weller WDC – Dry Cleaner The solution for cleaning from lead free solder! For further information see page 182.
Accessory:		
005 13 840 99		Brass wool WDC replacement (2 pieces)



Order No.	Model	Description
005 41 734 99	DIL 16WG	Desoldering tip for Dual-In-Line 310°C 7,62 x 2,54 mm
005 13 040 99	DS 7	Desoldering attachment 370°C
005 13 804 99		Spare triplet for desoldering attachment DS 7, Ø 1,5 mm

