

Thrust ball bearings, single direction

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Minimum load factor A	Speed ratings		Mass kg	Designation
d	D	H	dynamic	static			Reference speed	Limiting speed		
mm			kN		kN	-	r/min			-
12	26	9	10,4	16,6	0,62	0,0014	9000	13000	0,022	51101

