





ACCESSORIES PREFIX "Z"											
5	BUSHING WITH THROUGH HOLE 3,1 DIA.	2					2				
5	BUSHING WITH INNER THREAD 4-40 UNC		2					2			
5	BUSHING WITH INNER THREAD M3			2					2		
4	FEMALE SCREWLOCK WITH 4-40 UNC				2					2	
4	FEMALE SCREWLOCK WITH M3					2					2
7	BOARDLOCK	2	2	2	2	2					
ITEM NO.	DESCRIPTION OF ACCESSORY										
25 POS.-----> Z-106507-Y 		0-XXXXXX-Y	1-XXXXXX-Y	2-XXXXXX-Y	3-XXXXXX-Y	4-XXXXXX-Y	5-XXXXXX-Y	6-XXXXXX-Y	7-XXXXXX-Y	8-XXXXXX-Y	9-XXXXXX-Y
HOW TO ORDER:											
PLATING SUFFIX "Y"		GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652) SOLDERPART :2,5 μm TIN OVER NICKEL									
NOTES :		① GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD; WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD. ② CAVITY IDENTIFICATION AT FRONT SIDE ONLY. ③ PARTNUMBER AND DATE CODE. 4. AIR AND CREEPAGE DISTANCES ACCORDING TO DIN 41652.									
ITEM NRS./MATERIAL :		① SHELL : BRIGHT TINPLATED STEEL ② HOUSING : GLASSFILLED POLYESTER, COLOR : BLACK ③ CONTACTS : PHOSPHORBRONZE (PLATING : SEE TABLE ABOVE) ④ FEMALE SCREWLOCK : TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3) ⑤ BUSHING : TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3 OR 3,1 DIA THRU-HOLE) ⑥ BRACKET : TINPLATED STEEL ⑦ BOARDLOCK : TINPLATED PHOSPHORBRONZE ⑧ POST ALIGNMENTPLATE : GLASSFILLED NYLON. COLOR : BLACK									

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D. KESSLER CHK W. SOOMERS APVD —		14JAN99		 TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC — APPLICATION SPEC —		HD-20 SIZE 3 RIGHT ANGLE RECEPTACLE HEADER; MARK II+			
MATERIAL —		FINISH —		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C=106507	RESTRICTED TO —
CUSTOMER DRAWING							SCALE NTS	SHEET 1 of 1	REV 12