

## Screw connection - WP-G HF IP66 PG7 BK - 3240888

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland, Pg thread, IP66 protection, straight

The figure shows the WP-G HF IP66 M10 BK version



### Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 709958
Weight per Piece (excluding packing)	4.04 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	32.5 mm
Width (a)	17 mm
Wrench size	16.00 mm
Outside diameter	10.00 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

#### General

Color	black
Type	Straight
	Outer thread
Components	free from silicone, halogen, and cadmium

# Screw connection - WP-G HF IP66 PG7 BK - 3240888

## Technical data

### General

Inflammability class according to UL 94	V0
Material	PA

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

#### Approvals

UL Recognized / VDE Zeichengenehmigung / LR

---

#### Ex Approvals

---


#### Approvals submitted


---

#### Approval details

## Screw connection - WP-G HF IP66 PG7 BK - 3240888

### Approvals

UL Recognized 

VDE Zeichengenehmigung 

LR

### Accessories

#### Accessories

#### Corrugated pipe

Protective hose - WP-PA HF 10,0 BK - 3240680



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 10,0 BK - 3240838



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m