



ENGLISH

Datasheet

RS Pro RS1319A Digital Thermometer, 1 Input Recording, K Type Input

RS Stock No: **103-433**



Product Details

RS Pro digital thermometer has °C/°F selectable display, dual LCD display that helps to read temperature and maximum/minimum/average or offset reference value. It operates at a range of 0 to +40°C. It has 1 input recording, which is K type input. This instrument can be calibrated with probes listed as a system calibration.

Features and Benefits

- Data memory and read function direct from the display
- Display hold function
- Auto power off to conserve battery life
- Flip up stand
- Input protection 20 V maximum

**Specifications:**

Absolute Maximum Temperature Measurement	+1300°C
Application	Industrial
Battery Type	AAA
Best Accuracy	±0.75%
Data Storage	150 Sets
Dimensions	135 x 72 x 31 mm
Height	31 mm
Intrinsically Safe	No
Length	135 mm
Minimum/Maximum Recordings	Yes
Number of Temperature Inputs	1
Probe Type	K
Resolution	0.1°C
Temperature Scale	Centigrade, Fahrenheit
Thermometer Type	Recording
Weight	235 g
Width	72 mm
Input Protection	20 V
Instrument Measurement Range	-50 to +1300°C