

EK ECUH 180 G



Sample photo

Order symbol:	EKUH 180 G
Product nbr:	2538073
Description:	Enclosure, PC
Remarks:	Grey cover

EAN:	6418074013675
El. number:	
Finland:	3425434
Electric No. Italy:	7501070
Electric No. Sweden:	2538073

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	560	380	180	EKUH Base, PC
inch:	22.0	15.0	7.1	EKUN Base, PC
Materials:				EKU 30-G Cover
Material:	Polycarbonate			EKU 30-T Cover
Base colour:	RAL 7035 -light grey			EKUVT Mounting plate
Cover screws material:	Polyamide			EKUXT Mounting plate isolated
Cover colour:	RAL 7035 -light grey			EKV 32 DIN-35 Mounting rail
Cover screws colour:	Grey			EKUZR Extension frame
Gasket material:	Polyurethane			
Temperatures:				Rating:
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66/IP67
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK08
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1
Accessories:				UV resistance: UL 508
EKUM	Base, PC			Flammability Rating: UL 746C 5"
				Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
Certificates:				
				SGS Fimko
				Gost R

EK 560x380x180

