

iglidur® X – The High-Tech Problem Solver



Temperature resistant from -100°C to +250°C in continuous operation

Universal resistance to chemicals

High compressive strength

Very low moisture absorption

Excellent wear resistance through the entire temperature range



Large Kit contains:

| Type | Part Number | Norminal Bore (mm) | Bush OD (mm) | Flange OD (mm) | Flange Thickness (mm) | Overall Length (mm) | Qty |
|---------------|--------------|--------------------|--------------|----------------|-----------------------|---------------------|-----|
| Sleeve | XSM-0608-06 | 6 | 8 | | | 6 | 12 |
| Sleeve | XSM-0810-08 | 8 | 10 | | | 8 | 10 |
| Sleeve | XSM-1012-08 | 10 | 12 | | | 8 | 10 |
| Sleeve | XSM-1214-10 | 12 | 14 | | | 10 | 8 |
| Sleeve | XSM-1517-10 | 15 | 17 | | | 10 | 4 |
| Sleeve | XSM-2023-15 | 20 | 23 | | | 15 | 4 |
| Flanged | XFM-0608-08 | 6 | 8 | 12 | 1 | 8 | 10 |
| Flanged | XFM-0810-05 | 8 | 10 | 15 | 1 | 5.5 | 8 |
| Flanged | XFM-1012-09 | 10 | 12 | 18 | 1 | 9 | 6 |
| Flanged | XFM-1214-09 | 12 | 14 | 20 | 1 | 9 | 4 |
| Flanged | XFM-1517-12 | 15 | 17 | 23 | 1 | 12 | 4 |
| Flanged | XFM-2023-11 | 20 | 23 | 30 | 1.5 | 11 | 4 |
| Thrust Washer | XTM-1018-010 | 10 | 18 | | | 1 | 8 |
| Thrust Washer | XTM-1224-015 | 12 | 24 | | | 1.5 | 8 |
| Thrust Washer | XTM-1426-015 | 14 | 26 | | | 1.5 | 6 |
| Thrust Washer | XTM-1524-015 | 15 | 24 | | | 1.5 | 6 |
| Thrust Washer | XTM-1832-015 | 18 | 32 | | | 1.5 | 4 |
| Thrust Washer | XTM-2036-015 | 20 | 36 | | | 1.5 | 4 |