



ENGLISH

Datasheet

Stock No: 466-251

RS Pro 2 Pole Auxiliary Contact , NO/NC, 16 A



Product Details

Accessories

All switches rated at AC22

Auxiliary neutral 25A-36A rear mount for door interlocks and boxed isolators, front mount for panel mount isolators

Auxiliary change over contacts 20A-63A rear mount for door interlock and boxed isolators

Main Pole contact 25A-63A front mount for panel isolators, rear mount for door interlock and boxed isolators

Rubber gasket improves the ingress protection rating to IP65 on panel mount and door interlock devices.

Approvals

UL, CSA

Specifications:

Number of Poles	2
Maximum Current	16A
Normal State Configuration	NO/NC
Electrical Phase	1
Minimum Operating Temperature	-25°C
Handle Colour	n.a.
Maximum Operating Temperature	+40°C