

## Specification Grade Dead Front GFCI, Black

2085BK



GFCI DEAD FRONT, 10kA SCCR, 20A  
125VAC, Black

### features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. GFCIs with Auto-Ground assure a positive ground to metal box.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### specifications

#### General Info

Color: Black  
Type: Dead Front GFCI  
Style: Decorator

#### Listing Agencies/Third Party Information

cULus: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121614

### **Dimensions**

Depth U S: 0.98"  
Height U S: 4.2"  
Width U S: 1.72"

### **Technical Information**

Amps: 20A  
NEMA Configuration Number: 5-20R  
NEMA Rating: Yes  
Volts: 125V  
Volts A C: 125  
Grade Type: Specification

### **Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No