



Datasheet

Stock No: 340-3238

ENGLISH

RS Pro Manual Ball Valve Nickel Plated Brass 1/2 in BSPP



Product Details

Ball Valve with Strainer

- Epoxy coated Aluminium Tee Handle
- 18/8 Stainless steel strainer with 0.65mm perforations
- Female ports both ends

Ball Valves 1/4 Turn, WRC Approved, Tee Handle

Hot pressed, nickel plated brass full bore ball valves with Lever style operating handles. Suitable for oil, air, water, saturated steam or high temperature hot water services in domestic, commercial and industrial applications.

- Approved to WRC standards
- Red colour-coded 'Tee' handles
- Working Temperature Range (Fluid): -20 to +150°C

Specifications:

Threaded Connection:	1/2 in BSPP
Attachment Type:	Threaded
Body Material:	Nickel Plated Brass
Thread Size:	1/2in
Safe for Use With:	Air, Oil, Steam, Water
Maximum Working Pressure:	20 bar
Handle Colour:	Red
Ball Material:	Brass
Thread Standard:	BSPP
Handle Material:	Aluminium Alloy