



ENGLISH

Datasheet

Stock No: 808-567

Noga 1/4in Compressed Air Operated Coolant Spray



Product Details

Compressed-Air-Operated Coolant Spray

- Powered by compressed air, this unit provides a fine spray of coolant during drilling and cutting operations.
- Maximum heat dissipation gives extended tool life
- Magnetic base and can be mounted on round or square surfaces
- The air and coolant volumes have separate control valves that can be infinitely adjusted to provide output from a very fine mist to a heavy spray
- Air connection is via a 1/4 BSP connector
- Should the suction hose or filter become clogged it is easily cleaned by blocking the output nozzle. This will cause the compressed air to go down the suction hose and unblock it
- Air requirement 40 psi minimum, 100 psi maximum



ENGLISH

Specifications:

Type	Compressed Air Operated Coolant Spray
Systems	1/4in
Kit Contents	Magnetic Base, Valve, 2 Hoses, 340mm Flexi Hose