

Datasheet

RS Pro Non-Fused Terminal Block, 3 Way/Pole, Screw Down Terminals, 2.5 mm², Nylon, 250 V

RS Stock No: **492-4679**



Product Details

RS Pro non-fused terminal block has polyamide PA66 body with nickel plated brass inserts and plated steel screws. This 3-way block is suitable for use in high ambient temperatures. The temperature rating quoted for the rectangular types is with respect to the brass inserts. This terminal block with 2.5 mm² wire, features screw down termination. The block with 250 V voltage rating, has brass contact with nickel plating.

Features and Benefits

- Overall diameter of 16 mm
- Clamping area of 6 mm²
- Nominal cross sectional 2.5 mm²

**Specifications:**

Contact Material	Brass
Contact Plating	Nickel
Current Rating	10 A
Material	Nylon
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-40°C
Number of Ways	3
Termination Method	Screw Down
Voltage Rating	250 V
Wire Size	2.5 mm ²
Standards Met	RoHS, CE, UL 94V-0