

Order codes

Hardware/options coding



Basic Product

3216	48 x 48mm unit
3208	48 x 96mm unit
32h8	96 x 48mm horizontal unit
3204	96 x 96mm unit

1 Function

CC	Standard controller
CP	Standard programmer
VC	Motorised valve controller
VP	Motorised valve programmer

2 Supply Voltage

VH	85-264V ac
VL	24V ac or dc

3 Outputs

3216			
	OP1	OP2	
XXXX	None fitted	None fitted	
LXXX	Logic	None fitted	
LRXX	Logic	Relay	
RRXX	Relay	Relay	
LLXX	Logic	Logic	
LDXX	Logic	0-20mA	
DRXX	0-20mA	Relay	
RCXX	Relay	Isolated 0-20mA	
LCXX	Logic	Isolated 0-20mA	
DCXX	0-20mA	Isolated 0-20mA	
Not available with Low Voltage PSU			
DDXX	0-20mA	0-20mA	
LTXX	Logic	Triac	
TTXX	Triac	Triac	
3208/32h8/3204			
	OP1	OP2	OP3
LRRX	Logic	Relay	Relay
RRRX	Relay	Relay	Relay
LRDX	Logic	Relay	0-20mA
RRDX	Relay	Relay	0-20mA
LLDX	Logic	Logic	0-20mA
LDDX	Logic	0-20mA	0-20mA
RDRX	Relay	0-20mA	Relay
DRDX	0-20mA	Relay	0-20mA
Not available with Low Voltage PSU			
LLRX	Logic	Logic	Relay
DDDX	0-20mA	0-20mA	0-20mA
LTRX	Logic	Triac	Relay
TTRX	Triac	Triac	Relay
LTDX	Logic	Triac	0-20mA
TDDX	Triac	0-20mA	0-20mA
TTDX	Triac	Triac	0-20mA

4 AA Relay (OP4)

X	Not fitted
R	Relay
A	Dual relay (From A-OP3 and OP4)

5 Options Board

XXX	None fitted
XXL	Logic input
XCL	CT + Logic IP
2XL	RS232 Comms + Logic IP
4XL	2-wire RS232 comms + Logic IP
2CL	RS232 Comms CT + Logic IP
4CL	2-wire RS232 Comms CT + Logic IP

6 Fascia Colour

G	Green
S	Silver
W	Washdown (not 32h8/04)

7 Product Language

ENG	English
FRA	French
GER	German
SPA	Spanish
ITA	Italian

8 Manual Language

ENG	English
FRA	French
GER	German
SPA	Spanish
ITA	Italian

9 Warranty

XXXXX	Standard
WL005	Extended

10 Certificates

XXXXX	None
CERT1	Certificate of Conformity
CERT2	Factory Calibration Certificate

11 Custom Label

XXXXX	None
--------------	------

12 Specials and Accessories

XXXXX	None
RES250	250R resistor for 0-5V dc OP
RES500	500R resistor for 0-10V dc OP

3200 Accessories

HA029714	Installation guide
HA027986	Engineering manual
SUB35/ACCESS/249R.1	2.49R Precision resistor
CTR100000/000	10A Current transformer
CTR200000/000	25A Current transformer
CTR400000/000	50A Current transformer
CTR500000/000	100A Current transformer
iTools/None/3000CK	Configuration clip
SUB21/IV10	0-10V input adaptor

