

MNX PC 175/100 HG



Sample photo

Order symbol: PC 175/100 HG
Product nbr: 6011321
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022226
EI. number:
 Finland: 3420363
 Electric No. Denmark: 8212022218
 Electric No. Italy: 7351115
 Electric No. Sweden: 2535566

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Length	Width	Height	Accessories:		
mm:	180	180	100			MIN 15	DIN-15 Mounting rail	
inch:	7.1	7.1	3.9			MIV 15	DIN-35 Mounting rail	
							FP A 175/180	Front plate (Aluminium)
							HFP 180	Front plate hinge series
							FP 22046	Wall fastening lug (4 pcs)
Materials:								
Material:	Polycarbonate							
Base colour:	RAL 7035 -light grey							
Cover screws material:	Polyamide							
Cover colour:	RAL 7035 -light grey							
Cover screws colour:	Grey							
Gasket material:	TPE							
Temperatures:								
Temperature °C (short term):	-40 ... 120 °C							
Temperature °C (continuous):	-40 ... 80 °C							
Temperature °F (short term):	-40 ... 250 °F							
Temperature °F (continuous):	-40 ... 175 °F							
Accessories:								
MIV 175	Mounting plate (Galvanized steel)							
Rating:								
			Ingress Protection (EN 60529): IP66/IP67					
			Impact Resistance (EN 62262): IK08					
			Electrical insulation: Totally insulated					
			Halogen free (DIN/VDE 0472, Part 815): 1					
			UV resistance: UL 508					
			Flammability Rating: UL 746C 5V					
			Glow Wire Test (IEC 695-2-1) °C: 960					
			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13					
Certificates:								
			Germanischer Lloyd (GL)					
			SGS Fimko					
			Gost R					

