

UL CAB UL CAB PC 405020 G



Order symbol:	UL CAB PC 405020 G
Product nbr:	8143361
Description:	UL Cabinet, PC
Remarks:	Latches on the short side, smooth

EAN:	6418074053886
El. number:	
Finland:	
Electric No.	8212034170
Denmark:	
Electric No. Italy:	7821050U

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Sample photo

Dimensions:	Length	Width	Height
mm:	400	500	200
inch:	15.7	19.7	7.9

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	EPDM

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5V
UL Type:
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:

- Germanischer Lloyd (GL)
- Underwriters Laboratories
- SGS Fimko
- Lloyds Register of Shipping (LR)
- UL Canada
- Gost R

CAB 500x400x200

