

Datasheet

Art.No. 80.063.4032.1

Relay FLARE MOVE 38 24DC6A AU

pluggable relais flare MOVE, nominal operating voltage 24V DC, output 48V 20mA, gold-plated contacts



Art.No.	80.063.4032.1
EAN	4015573659346
Order unit	10 pieces

Approvals

Technical data

General

Connection type	Plug-in connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	No
Degree of protection (IP)	IP20

Technical data

Type of excitation	
Nominal voltage DC	24 V
Lower nominal voltage DC	24 V
Upper nominal voltage DC	24 V

Dimensions

Depth	15 mm
Width	5 mm
Height	28 mm

**Classification**

ECLASS 8.1	27371601: Switching relay
ETIM 5.0	EC001437: Switching relay
ETIM 4.0	EC001437: Switching relay
ETIM 3.0	EC001437: Switching relay