




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	RELEASED PER EC 0S13-0087-05	08SEP05	GP	JG




- 1 HOUSING: BLACK POLYESTER, UL 94V-0 RATED.
CONTACTS: PHOSPHOR BRONZE.
- 2 GOLD FLASH FOR A LENGTH OF 2.54[.100] MIN FROM
MATING END, 2.54 μm [.000100] MIN TIN FOR A LENGTH OF
3.18[.125] FROM OPPOSITE END, ALL OVER 1.27 μm [.000050]
MIN NICKEL.
- 3 0.76 μm [.000030] MIN GOLD FOR A LENGTH OF 2.54[.100] MIN FROM
MATING END, 2.54 μm [.000100] MIN TIN FOR A LENGTH OF
3.18[.125] FROM OPPOSITE END, ALL OVER 1.27 μm [.000050]
MIN NICKEL.



RECOMMENDED PC BOARD MOUNTING DIMENSIONS

**COPYRIGHT 2005
TYCO ELECTRONICS CORP
ALL RIGHTS RESERVED**



3	5207828-4
2	5207828-3
CONTACT FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. PETERS 08SEP05		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK S. BOLASH 08SEP05			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, SIZE 3, 25 POSN, VERTICAL, AMPLIMITE HD-20	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°			
MATERIAL		FINISH			
		CONTACTS: SEE TABLE			
		DWN M. WALMSLEY 08SEP05		SIZE A2	
		PRODUCT SPEC 108-40025		CAGE CODE 00779	
		APPLICATION SPEC -		DRAWING NO C-5207828	
		WEIGHT -		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1	
				SHEET 1 of 1	
				REV 0	