



Security Tech Germany

80TI/40mm TITALIUM™ Padlocks

- High quality TITALIUM™ body with stainless steel appearance : Maximum corrosion resistance
- 6 Pin tumbler cylinder with anti-pick mushroom pins : Resists picking
- Through hardened steel alloy shackle : Resists saw attacks
- Rustfree internal components & chrome plated cylinder : Durable security
- Large tulip shaped keyhead : Convenient security
- Numerous KA suites available : Multiple site security
- Available blister packed or boxed : Informative generic packaging



Paracentric Keyway Saw Resistant Double Bolted Keyed Alike Available



80TI/40 with 110/155 Hasp & Staple



"NanoProtect" Chrome Plating Helping to make rusty shackles a thing of the past

The flagship of the TITALIUM™ family of padlocks makes an impression with both its look and its technical properties. Within a massive lock body is a 6-pin precision cylinder with paracentric keyway giving protection against both forced or manipulative break-ins. A chrome plated cylinder core and hardened steel shackle with NANO Protect shackle coating assures security & high corrosion resistance.



80TI/40

ABUS UK Product Reference	ABUS Code	ABUS GPS	D mm	H mm	L mm	D mm	H mm	L mm	Weight gms	Key Blank	
										Reference	Code
80TI/40 Titanium Padlock	56220	6	20	40	7	40	89.5	19	130	80TI/40+45+50	57862
80TI/40HB63 Titanium Padlock	56227	6	20	63	7	40	112.5	19	170	80TI/40+45+50	57862
80TI/40 KA8011 Titanium Padlock	56221	6	20	40	7	40	89.5	19	130	80TI/40+45+50	57862