



40367 - OT*Q75PAR30 240V E27 10DEG GE BX1/15

• Specifications

General characteristics:

Wattage [W]	75
Voltage [V]	240
Cap/Base	E27
Bulb Shape	PAR
Bulb Diameter [mm]	97
Colour temperature [K]	2900
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	2000
Dimming Capability	Yes
Coil type	CC-8
Beam Angle [°]	10
Center Beam Candlepower [cd]	6900
Maximum Overall Length [mm]	88
DUN Code	10043168403679
EAN Code	0043168403672
Net weight per piece [g]	175
Gross weight per piece [g]	258
Pack Quantity	15
Layer quantity EUR (PC)	60
Layer quantity UK (PC)	75
Pallet quantity EUR (PC)	360
Pallet quantity UK (PC)	450
Outer case size	525 x 340 x 175 (mm)
Energy Efficiency Class	F
Brand	General Electric (GE)