

PLC-BSP- 24DC/21-21

Order No.: 2912439



14 mm PLC basic terminal blocks with spring-cage connection
method, input voltage 24 V DC (without relay or optocoupler)

Commercial data

EAN	4046356050845
Pack	10 pcs.
Customs tariff	85364190
Weight/Piece	0.05043 KG

Product notes

WEEE/RoHS-compliant since:
04/10/2006



[http://](http://www.download.phoenixcontact.com)

www.download.phoenixcontact.com
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data**Input data**

Nominal input voltage U_N	24 V DC
Status display	LED
Protective circuitry	Polarity protection Polarity protection diode

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Type of connection	Spring-cage connection
Stripping length	8 mm

General data

Length	80 mm
Width	14 mm
Height	94 mm
Color	green
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Operating mode	100% operating factor
Inflammability class acc. to UL 94	V0
Mounting position	Any
Assembly instructions	In rows with zero spacing

Certificates / Approvals

Certifications applied for: UL Listed / CUL Listed

Address

PHOENIX CONTACT UAB
Svitrigailos Str. 11b
03228 Vilnius, LITHUANIA
Phone +370 5 2106321
Fax +370 5 2106324
<http://www.phoenixcontact.lt>



© 2009 Phoenix Contact
Technical modifications reserved;