

Test plugs - MPS-MT - 0201744

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test plugs, Color: silver

Why buy this product

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm diameter
- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 098803
Weight per Piece (excluding packing)	1.4 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Length	5 mm
Length contact range	10.85 mm
Width	5 mm
Pin diameter	2.30 mm
Note on dimensions	Length without insulating sleeve

General

Color	silver
Material	silver-plated brass
Minimum temperature	-40 °C
Maximum temperature	125 °C
Voltage	60 V DC

Test plugs - MPS-MT - 0201744

Technical data

Additional text	30 V AC
Current	10 A

Classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27141148

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC002255
ETIM 5.0	EC002555

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

Test plugs - MPS-MT - 0201744

Approvals

EAC
