


Datasheet

PET, Rubber Vee Friction Belt, belt section A

RS Stock number 472-026

A Section Classical Wrapped Vee Belts

to API 1B, RMA IP 20, DIN 2215, ISO 4184 & BS3790



Dimensions w x h (mm)	Min. Pulley Diam. PCD (mm)	Std. Belt Lengths (mm)
13 x 8	80	540 - 4600

Description:

RS Z, A & B Section Belts

Special compounded stiff-yet-flex-crack resistant base

High modulus low stretch (hmls) polyester cords and length stabilisation process resulting in low stretch and maximum life

Polychloroprene impregnated poly-cotton jacket

Precision built belts requiring no matching or coding

Anti-static, heat, oil and abrasion resistant

Standards: API 1B, RMA IP 20, DIN 2215, ISO 4184 & BS3790

Specifications:

Belt Section:	A
Height:	8mm
Length:	610mm
Material:	PET, Rubber
Minimum Pulley Diameter:	80mm
Top Width:	13mm



A Section - 13mm x 8mm - Wrapped Construction

Inside Length Li (ins)	Inside Length Li (mm)	Inside Length Li (ins)	Inside Length Li (mm)	Inside Length Li (ins)	Inside Length Li (mm)	Inside Length Li (ins)	Inside Length Li (mm)
A10	254	A38	965	A69	1750	A110	2800
A11	280	A38.5	975	A70	1775	A112	2845
A12	305	A39	990	A71	1800	A113	2870
A13	330	A39.5	1000	A72	1825	A114	2896
A14	355	A40	1016	A73	1854	A115	2921
A15	381	A40.5	1030	A74	1880	A116	2946
A16	407	A41	1041	A75	1900	A118	3000
A17	432	A41.5	1050	A76	1930	A120	3048
A18	457	A42	1060	A77	1956	A122	3100
A19	480	A42.5	1075	A78	1980	A124	3150
A20	508	A43	1100	A79	2000	A126	3200
A21	535	A43.5	1104	A80	2032	A128	3250
A22	560	A44	1120	A81	2060	A130	3300
A22.5	575	A45	1143	A82	2083	A132	3350
A23	585	A45.5	1150	A83	2110	A134	3400
A23.5	600	A46	1168	A83.5	2120	A136	3454
A24	610	A46.5	1180	A84	2134	A138	3500
A25	630	A47	1200	A85	2160	A140	3550
A25.5	650	A47.5	1215	A86	2180	A144	3658
A26	660	A48	1220	A87	2210	A148	3750
A26.5	670	A48.5	1225	A88	2240	A150	3810
A27	686	A48.75	1240	A89	2260	A153	3886
A27.5	700	A49	1250	A90	2286	A155	3937
A28	710	A50	1270	A91	2310	A158	4000
A29	730	A51	1300	A92	2337	A162	4115
A29.5	750	A52	1320	A93	2360	A165	4200
A30	767	A53	1350	A94	2388	A167	4250
A30.5	775	A54	1375	A95	2413	A170	4318
A31	787	A55	1400	A96	2438	A173	4394
A31.5	800	A56	1422	A97	2464	A176	4470
A32	813	A57	1450	A98	2500	A177	4500
A32.5	825	A58	1475	A99	2515	A180	4572
A33	838	A59	1500	A100	2540	A185	4700
A33.5	850	A60	1525	A101	2565	A187	4750
A34	864	A61	1550	A102	2591	A190	4825
A34.5	875	A62	1574	A103	2616	A195	4950
A35	889	A63	1600	A104	2650	A197	5000
A35.5	900	A64	1625	A105	2667	A200	5080
A36	914	A65	1650	A106	2692	A217	5512
A36.5	925	A66	1676	A107	2725		
A37	940	A67	1700	A108	2743		
A37.5	950	A68	1725	A109	2769		