

Datasheet

RS Pro Straight 50Ω PCB Mount BNC Connector, jack, Solder Termination Nickel

RS Stock No: **546-5187**



Product Details

RS Pro PCB mount BNC connector has a nickel plated body and gold plated centre contact. This 50 Ω straight BNC connector comes with cable jack, solder termination.

Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Jack, solder termination

Specifications:

Body Orientation	Straight
Body Plating	Nickel
Contact Material	Phosphor Bronze
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mounting Type	PCB Mount
Operating Frequency	0 to 1 GHz
Polarity	Normal
Termination Method	Solder
Body Material	Zinc Alloy
Contact Resistance	1.5 m Ω (Maximum Central), 0.5 m Ω (Maximum Outer)
Insulation Material	PTFE (Internal)
Insulation Resistance	5000 M Ω
Number of Functions	500
Operating Temperature Range	-65 to +85°C
Standards Met	RoHS Compliant
Voltage Rating	750 V (Insulation), 335 V (Working)