

## Datasheet

# RS Pro Insulated Crimp Spade Connector, 2.5mm<sup>2</sup> to 6mm<sup>2</sup>, 12AWG to 10AWG, M4 Stud Size, Yellow Vinyl

RS Stock No: 149-518



## Product Details

RS Pro insulated crimp spade connector in yellow vinyl colour, has 2.5 mm<sup>2</sup> to 6 mm<sup>2</sup>, 12 to 10 AWG wire size and M4 stud size. This connector has a PVC funnel entry range of crimps on reels. It is available in a variety of the most popular sizes.

## Features and Benefits

- PVC funnel entry range of crimps on reels
- Available in a variety of the most popular sizes
- Red 0.5 to 1.5 mm<sup>2</sup>, blue 1.5 to 2.5 mm<sup>2</sup> and yellow 4 to 6 mm<sup>2</sup>

**Specifications:**

Colour	Yellow
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	10 AWG
Maximum Wire Size (mm <sup>2</sup> )	6 mm <sup>2</sup>
Minimum Wire Size (AWG)	12 AWG
Minimum Wire Size (mm <sup>2</sup> )	2.5 mm <sup>2</sup>
Overall Length	24.2 mm
Stud Size	M4.3
Thickness	1 mm
Width	7.2 mm
Wire Size	12 to 10 AWG
Current Rating	48 A
Temperature Rating	+75°C
Type	Flared Vinyl without Copper Sleeve
Voltage Rating	600 V