





REV.	CNN	CNN DESCRIPTION	Date	Check in
02	-	ROHS MISSING	19/01/2010	Shaun Barron
02	-	BORDER CHANGE	20/01/2010	Shaun Barron



SPECIFICATIONS

VOLTAGE 500Vac
FREQUENCY 50/60Hz
CURRENT 36A @ 40°C
TEMPERATURE -25 TO 100°C
LEAKAGE CURRENT 81mA @ 500V 50Hz
HUMIDITY 90% RH (NON-CONDENSING)
VIBRATION 10-200Hz 1.8G
ELECTRIC STRENGTH 2250Vac/1min.
POWER DISSIPATION 16W
MASS 2.7kg
TERMINALS 10sqmm TERMINAL BLOCK
EARTH TERMINALS M6 STUD
FLANGE MOUNTING 4x M6



RoHS
2002/95/EC
Compliant

Tel No.+44(0)1724273200 Website www.dem-uk.com



DEM Manufacturing, Deltron Emcon House
Hargreaves Way, Sawcliffe Ind. Park,
Scunthorpe, North Lincolnshire, DN15 8RF, UK

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
ALPHA 3 MANUFACTURING.
ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN
PERMISSION OF
ALPHA 3 MANUFACTURING IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETRES
LINEAR TOLERANCE:
NO DECIMAL PLACES $\pm 0.5\text{mm}$
1 DECIMAL PLACE $\pm 0.25\text{mm}$
2 DECIMAL PLACES $\pm 0.125\text{mm}$
ANGULAR TOLERANCE: $\pm 1^\circ$

FINISH

-

DEBURR AND
BREAK SHARP
EDGES

DRAWN BY

AT

APPROVED BY

AT

THIRD ANGLE PROJECTION



IF IN DOUBT ASK
DO NOT SCALE DRAWING

MATERIAL

-

TITLE

GENERAL SPECIFICATION
3 PHASE 36A 500V
INDUSTRIAL FILTER

DRAWING NO.

KMF336A

ISSUE

02

Release