

Rittal – The System.

Faster – better – everywhere.

► Hygienic Design Compact enclosure HD – HD 1302.600

Date : Nov 27, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Hygienic Design Compact enclosure HD – HD 1302.600

: 27.11.2017 build on www.rittal.com/ca-en



Product description

Version:	Roof slope 30° towards the front
Material:	Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel Lock inserts HD: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish:	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated Seal: Blue, dyed (RAL 5010)
Protection category IP to IEC 60 529:	IP 66
Protection category IP to DIN 40 050-9:	IP 69K
Protection category NEMA:	NEMA 13 NEMA 4X
Supply includes:	Housing of all-round solid construction Door with fitted seal Door catch on right, may be swapped to the left Mounting plate
Base material:	Stainless steel

Product features

Dimensions:	Height (front): 350 mm (14 ") Height (rear): 437 mm (17 ") Width: 220 mm (8.7 ")
--------------------	--

Depth: 155 mm (6.1 ")

Mounting plate:	Height: 275 mm (11 ") Width: 162 mm (6.4 ")
Number of cam locks:	1
Packaging unit:	1 pc(s).
Weight/packaging unit:	6.6 kg (14.6 lb.)
EAN:	4028177567597
Customs tariff number:	94032080
ETIM 6.0:	EC000261
ETIM 5.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 7.0/7.1:	27180101
eCl@ss 6.0/6.1:	27180101
eCl@ss 5.1/5.1.4:	27180102
Product description (long):	HD Compact enclosure, WHD: 220x350(H1)x437(H2)x155 mm, Stainless steel 1.4301, with mounting plate, with hinged door and silicone seal
Approvals	
Approvals:	UL + C-UL
Certificates:	DGUV EAC
Declarations:	Declaration of conformity