

Datasheet Step Ladders, 3 Tread

RS Stock number **877-6819**

- Foldable for easier storage.
- Working load: 150kg.
- Steel constructed framework
- Fitted with a rubber comfort handle.
- Non slip ribbed rubber treads/steps.
- Distance between Treads: 230mm.
- Fitted with plastic floor protectors.
- Powder coated silver/grey.



Description	Open size H x W x D (mm)	Folding size H x W x D (mm)	Tread W x D (mm)	Platform Height (mm)	RS Stock No.
Step Ladders 2 Tread	775 x 485 x 510	890 x 135 x 485	380 x 260	490	877-6815
Step Ladders 3 Tread	1065 x 490 x 665	1220 x 140 x 490	380 x 260	710	877-6819
Step Ladders 4 Tread	1290 x 490 x 830	1475 x 145 x 490	380 x 260	930	877-6828