

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19429-0030](#)
Status: **Active**
Overview: [MX150L™ Industrial Sealed Connector System](#)
Description: [MX150L™ 10 Circuit Panel Mount Plug for 14-22 AWG Wire, Through Hole Flange Assembly, without Gasket](#)

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[Product Specification PS-19417-001 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	19429
Application	Power, Wire-to-Wire
Comments	For Outside or Inside Panel Mount Application. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (
Overview	MX150L™ Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L™
UPC	822348544431

Physical

Circuits (maximum)	10
Gender	Plug
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Net Weight	18.000/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	18A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-19417-001
Sales Drawing	SD-19429-014



EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
 Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19429Series](#)

Mates With

[19418 Receptacle Assemblies](#)

Use With

[19417 Male Crimp Terminals](#)