




AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
150°C MAX

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
1.04-2.62mm² [2,050-5,180]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

- 5

DWN
JR RUTH
CHK
T MICHIELUTTI
APVD
T MICHIELUTTI
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

10JAN08
10JAN08
10JAN08

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

TERMINAL, RECTANGULAR TONGUE,
P.I.D.G.
WIRE SIZE: 16-14 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-130531

-

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV D

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

AMP 1470-19 REV 31MAR2000