

DO NOT SCALE

DIMENSIONS IN INCH

METRIC

THIRD ANGLE

PROJECTION





WIRE RANGE :

0,8-2,0mm² (18-14 AWG)



INSULATION RANGE :

3,30-4,45 (.130-.175)


DIA.



VIEW A-A



SECTION B-B



SECTION C-C

NOTES:

- 1 CONTINUOUS STRIP, ON REELS.
- 2 DIM'S IN BRACKETS ARE IN INCHES.

△ SPLICE-FREE.

TINPLATED	0,46 (.018) THK. BRASS	62734-4
SILVERPLATED	0,46 (.018) THK. BRASS	△ 62734-3
SILVERPLATED	0,46 (.018) THK. BRASS	62734-2
NONE	0,46 (.018) THK. BRASS	62734-1
FINISH	MATERIAL	PARTNUMBER

-	-	-	-	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-
D	EH-0359-96	M.V.A	A.B	14-03-96
C	H-10024	R.D.	R.D.	02-09-92
LTR.	REVISION RECORD	DR.	CHK.	DATE

CUSTOMER DRAWING FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION _____, 19____

AMP

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME

.156 DIA. PIN RECEPTACLE

DR.: R.DAAMEN CHK.: R.D.IKSTRA APP.: L.v.SOEEST
DATE: 02-09-92 DATE: 01-01-93 DATE: -

DWG.No.
C-62734

REV.LTR.

D

SHEET

1 OF 1

A4