

## Cable - CABLE-FLK14/OE/0,14/ 400 - 2305774

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Round cable assembled with a 14-pos. socket strip and an open end. On the open end, the wires are labeled with 1 to 14 and have ferrules, cable length: 4 m

The illustration shows a 50-pos. version

### Why buy this product

- 14 and 16-pos.
- Connector according to IEC 60603-13
- Open end at one end
- 1:1 connection

### Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 046356 039116 |
| Weight per Piece (excluding packing) | 236.8 g   |
| Custom tariff number                 | 85444290  |
| Country of origin                    | Germany   |

### Technical data

#### General

|   |   |
|---|---|
| Nominal voltage $U_N$                         | < 50 V AC   |
|   | 60 V DC   |
| Max. current carrying capacity per path       | 1 A   |
| Max. conductor resistance                     | 0.16 $\Omega$ /m                                    |
| Length of cable                               | 4 m   |
| Single wire, cross section                    | 0.14 mm <sup>2</sup>                                |
| AWG   | 26  |
| Conductor construction: Number of litz wires: | 7   |
| Single wire, material                         | Cu tin-plated                                       |
| Test voltage                                  | 0.8 kV  |
| External diameter                             | 6.4 mm  |
| Cable, preassembly                            | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |

# Cable - CABLE-FLK14/OE/0,14/ 400 - 2305774

## Technical data

### General

|           |    |
|-----------|----|
| Shielding | no |
|-----------|----|

### Environmental conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance                        | IEC 60332-1      |

### Connector, module side

|                     |                                |
|---------------------|--------------------------------|
| Number of positions | 14                             |
| Connectors          | IDC/FLK socket strip (2.54 mm) |
| Number of plugs     | 1                              |

### Connector, controller side

|                     |          |
|---------------------|----------|
| Number of positions | 14       |
| Connectors          | Open end |
| Number of plugs     | 0        |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27061801 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000830 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11     | 26121620 |
| UNSPSC 12.01  | 26121620 |
| UNSPSC 13.2   | 26121620 |

## Approvals

### Approvals

## Cable - CABLE-FLK14/OE/0,14/ 400 - 2305774

### Approvals

---

Approvals

UL Recognized / cUL Recognized / cULus Recognized

---


Ex Approvals


---


Approvals submitted

---

### Approval details

UL Recognized 

cUL Recognized 

cULus Recognized 

---