



- | | |
|---|--|
| 4 | 2.54 μm [.000100] MIN TIN, OVER
2.54 μm [.000100] MIN COPPER. |
| 5 | OBSOLETE |
| 6 | D DIMENSION APPLIES TO STYLE II OR STYLE III FERRULES ONLY. |
| 7 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

7 OBSOLETE

4805 (3/11)