

F

E

D

C

B

A

F




E

D

C

B

A





基板取付穴推奨寸法 (参考)
RECOMMENDED P.C. BOARD
HOLE DIMENSION (REFERENCE)

注記 NOTES

- 1. 嵌合相手 : 51004-**00
MATES WITH : 51004-**00
- 2. 3極以上のキンク加工については、トレードマーク側からキンク、ストレートの順に、1極おきに2箇所以上に施すこと。
KINK TO BE ADDED ON THE ODD NUMBER SOLDER TAILS. (FROM THE TRADE MARK SIDE.)
- 3. ロック用の穴は、2極品及び3極品に1ヶ、4極品以上は2ヶとする。
LOCKING HOLE : 1 PLACE FOR 2, 3 CKTS, 2 PLACES FOR 4 CKTS. AND MORE THAN 4 CKTS.

2極品のキンク形態図
KINK FORM FOR 2 CKTS.
両方のテールにキンクを施す。
SOLDER TAIL KINK SHOULD
BE ADDED ON BOTH TAILS.



ウェハー
WAFER
(ナイロン66、ガラス入り
NYLON66, GLASS FILLED)
UL94V-0
回路番号
CIRCUIT NO.
ピン
PIN
(リン青銅、鍍メッキ
PHOSPHOR BRONZE,
PRE-TINNED, t=0.32)

26	3	1.4	28	32	31.1	28	53014-1510	15
24	3	1.4	26	30	29.1	26	-1410	14
22	3	1.4	24	28	27.1	24	-1310	13
20	3	1.4	22	26	25.1	22	-1210	12
18	3	1.4	20	24	23.1	20	-1110	11
16	3	1.4	18	22	21.1	18	-1010	10
14	3	1.4	16	20	19.1	16	-0910	9
12	3	1.4	14	18	17.1	14	-0810	8
10	3	1.4	12	16	15.1	12	-0710	7
8	3	1.4	10	14	13.1	10	-0610	6
6	3	1.4	8	12	11.1	8	-0510	5
4	3	1.4	6	10	9.1	6	-0410	4
—	4	3.4	4	8	7.1	4	-0310	3
—	3	1.4	2	6	5.1	2	53014-0210	2
G	F	E	D	C	B	A	PLASTIC BAG	NO. OF CKTS.
							ORDER No. オーダー番号	

REVISED
EC NO: J2009-0377
DRWN: MWABE
CHKD: THARUYAMA
APPR: NUKITA
2008/08/07
2008/08/18
2008/08/19

DESCRIPTION
10 UNDER ±0.2
10 OVER 30 UNDER ±0.25
30 OVER ±0.3
ANGULAR ±3 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

DIMENSION STYLE
MM ONLY
DRAWN BY
M. HENMI
CHECKED BY
M. FUKUSHIMA
APPROVED BY
M. ENOMOTO
DATE
'92/03/06
'92/05/28
'92/05/28
MATERIAL NO.

SCALE
5:1
TITLE
2.0 LOW PROFILE
WAFER ASSY

DESIGN UNITS
METRIC
THIRD ANGLE
PROJECTION

53014-**10
MODEL NO.

MOLEX INCORPORATED
SD-53014-001

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SHEET NO.
1 OF 1