




2			1					
LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
			A	RELEASED		27-JUN-05	JM.CAO	YIP,A
			B	CHANGE TE LOGO AND ADD UL MARKING	ECO-08-013316	06-AUG-08	SZ,Z	BH,Y




PC BOARD LAYOUT(BOTTOM VIEW)



CONNECTION DIAGRAM (BOTTOM VIEW)



107-79007	1721548-4	LN313024	24V	LN313024	c
107-79007	1721548-3	LN313012	12V	LN313012	b
107-79007	1721548-1	LN313006	6V	LN313006	a
PACKAGE SPEC	TE PART NO	DESCRIPTION	PART B	PART A	TYPE



AR	AR	AR			EPOXY RESIN	SEAL	13
AR	AR	AR			UEW	MAGNETIC WIRE	12
1	1	1	UL 94V-0		PBT	CASE	11
1	1	1	UL 94V-0		PET	BOBBIN	10
1	1	1			CP WIRE	COIL TERMINAL	9
2	2	2			AgSnO ₂	STATIONARY CONTACT	8
1	1	1			AgSnO ₂	MOVABLE CONTACT	7
1	1	1			Cu	B-TERMINAL	6
1	1	1			Cu	M-TERMINAL	5
1	1	1			Cu ALLOY	MOVABLE SPRING	4
1	1	1		Ni PLATING	STEEL	CORE	3
1	1	1		Ni PLATING	STEEL	ARMATURE	2
1	1	1		Ni PLATING	STEEL	YOKE	1
c	b	a	INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

NOTE:
1.LOT NO. SYSTEM AS FOLLOWING:

0829

WEEK
YEAR

Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±
MATERIAL	FINISH
SEE MATERIAL TABLE	

DWN	JM.CAO	Tyco Electronics Corporation ShenZhen, China		
CHK	YIP.ANTHONY			
APVD	N.FUNAYAMA			
PRODUCT SPEC				
APPLICATION SPEC		LN3 Cd FREE TYPE CUSTOMER DRAWING		
WEIGHT				
CUSTOMER DRAWING		SIZE	GAGE CODE	DRAWING NO
		A3	00779	1721548
		RESTRIC TO		REV
		SCALE 4:1		B