



ENGLISH

Datasheet

**RS Pro Dolly, 625 x 420mm, 100kg Load**

RS Stock No: **760-4195**



## Product Details

RS Pro dolly measuring 625 x 420 mm, withstands load capacity of up to 100 kg. This dolly hand truck is suitable for the transportation of Euro containers 725-9167, 725-9161, 725-9170, 725-9158 and 725-9151.

## Features and Benefits

- Perfect to transport multiple containers without causing excessive strain
- Manufactured from ABS plastic
- Zinc finished steel adjustable handle
- Handle removable when not in use



ENGLISH

## Specifications:

Brakes	No
Frame Material	Plastic
Load Capacity	100 kg
Number of Levels	1
Overall Height	160 mm
Platform Dimensions	625 x 420 mm
Platform Length	625 mm
Platform Width	420 mm
Type	Dolly
Wheel Diameter	100 mm
Wheel Features	Swivel
Wheel Material	Nylon
Wheel Type	Castor